



REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
1		PRELIMINARY	11APR2016	TS GF
2		REV LABEL FORMAT	30AUG2016	TS GF
3		ADDED -5	09JAN2017	GF GF
4		ADDED NOTE 6	07JUL2017	TS GF



- CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFERENTIALLY)
  - CABLE ASSEMBLY TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.
  - PRODUCT AND PROCESSING MEETS THE REQUIREMENTS OF TE STANDARD TEC-138-702.
  - SEE SHEET 2 FOR WIRING SCHEMATIC.
- 5 LABEL INFORMATION: -1 SHOWN



6 DUE TO SHORT CABLE LENGTH, THE PART NUMBERS INDICATED MAY NOT MEET IEEE802.3bj MINIMUM INSERTION LOSS LIMITS.


1500±40	30 AWG	2821310-5
3000±40	30 AWG	2821310-4
2000±40	30 AWG	2821310-3
6 1000±40	30 AWG	2821310-2
6 500±25	30 AWG	2821310-1
L	WIRE GAGE	PART NO

**THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING**

**PRELIMINARY NOT RELEASED FOR PRODUCTION**

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN T. SMITH 11APR2016	STE Connectivity	
DIMENSIONS: mm		CHK G. FRANKLIN 11APR2016	NAME CABLE ASSEMBLY MICRO QSFP TO MICRO QSFP 30 AWG	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. FRANKLIN 11APR2016	PRODUCT SPEC	
0 PLC ±		APPLICATION SPEC		
1 PLC ±		SIZE CAGE CODE DRAWING NO		
2 PLC ±		RESTRICTED TO		
3 PLC ±		A1 - C=2821310		
4 PLC ±		SCALE 7:4 SHEET 1 OF 2 REV 4		
ANGLES ±		CUSTOMER DRAWING		
FINISH ±				

REVISIONS				
P.	LTN	DESCRIPTION	DATE	OWN APVD
		SEE SHEET 1		



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN T. SMITH 11APR2016	TE Connectivity
CHK G. FRANKLIN 11APR2016	
APVD G. FRANKLIN 11APR2016	
NAME CABLE ASSEMBLY MICRO QSFP TO MICRO QSFP 30 AWG	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL	FINISH
CUSTOMER DRAWING	

SIZE A1	CAGE CODE -	DRAWING NO. C=2821310	RESTRICTED TO
SCALE 7:4	SHEET 2	OF 2	REV 4