

CONNETTORE TIPO B (CON MOLLA DI RITEGNO INTERNA)

CONNECTOR TYPE B (WITH INTERNAL SPRING)

17.0 ±0.5

12.8 ±0.5

1.5 COST.

37.5 ±0.5

5.0 ±0.5

0.8 COST.

AMP

1

2

3

A

K

SEZIONE A-A
(SECTION A-A)

25° COST.

11.8 ±0.5

3.0 ±0.5

1.0

2.2

1.5

1.3

16.0 ±0.5

12.3 ±0.3

Ø0.9 ±0.05
SPRING WIRE
DIAMETER

TOP

VISTA DA K
(VIEW FROM K)

3.3 +0.3
-0.1

+0.2

1.6 -0.1

9.9 ±0.6

17.3 ±0.3
AT TOP

TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828905-1, 282536-1.
TAPPO CAVITA' P/N 828906-2
(TYP. CAV. FOR JPT CONT. P/N 929939-.. A/O 929937-.. AND REL.
SINGLE WIRE SEAL P/N 828904-1, 828905-1, 282536-1
CAVITY PLUG P/N 828906-2)

PASSO 5.0 ±0.15
(PITCH 5.0 ±0.15)

17.5 ±0.5

R 5.5 ±1.0

R 16.8 ±1.0

23.0 ±0.5

ASSE CAVITA'
(CAVITY CENTER LINE)

ASSE CONNETTORE
(CONNECTOR CENTER LINE)

OBSOLETE	ROSSO (RED)	282190-8							
OBSOLETE	GIALLO (YELLOW)	282190-7							
	MARRONE (BROWN)	282190-6							
OBSOLETE	BLU (BLUE)	282190-5	3	////		ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)		
	VERDE (GREEN)	282190-4							
OBSOLETE	NATURALE (NATUR)	282190-3	2	NATURALE (NATURAL)		GOMMA SILICONICA (SILICONE RUBBER)	GUARNIZIONE (RUBBER GASKET)		
	GRIGIO (GREY)	282190-2							
	NERO (BLACK)	282190-1	1	////		PA 6.6 C.VETRO (PA 6.6-GF)	BLOCCETTO (HOUSING)		
	COLORE COLOR	NUMERO PART. No	N (ITEM)	FINITURA / (FINISH / COLOUR)		MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Ennio CINI 9 NOV 90	TE Connectivity	
DIMENSIONS: mm		CHK C.TARTARI 13 OCT 92	2 W.SPLASH PROOF CONN.ASS'Y with SECONDARY LOCK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME	
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± 0.3		APPLICATION SPEC	-	
2 PLC ± -		WEIGHT	-	
3 PLC ± -		CUSTOMER DRAWING	-	
4 PLC ± -		SCALE NTS	SHEET 1 OF 2	
ANGLES ± 2°		REV M2		

METRIC	DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0mm (REDUCED INS.CABLE)	RANGO FILO (WIRE RANGE) 0.5-2.5 mm²
--------	---	---

CUSTOMER DWG. FOR REFERENCE ONLY	
DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	

1471-9 (3/11)

282190

1

2

