



△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D. RENAUD/D. SINISI

	STAGNATO	OTTONE	282332-2	D
△ 2	---	OTTONE	282332-1	E
	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)	REV

WIRE RANGE mm	REDUCED INS. CABLE (à IS. RID. FASE 3)
0.5	1.5-1.7
1.0	1.9-2.1
1.5	2.2-2.4

CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION	
c COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING			
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES: UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILI (WIRE RANGE)	SCALA (SCALE)
± 0.3	1.5-2.4 DIA	0.5-1.5 mm ²	5:1
ANGOLI (ANGLES)	AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)		
DIS. 22 JULY 1992 (DR.) C. IANNARELLI	DESCRIZIONE (DESCRIPTION) 197 SRS. FASTON REC. CONTACT		
D1 REV PER ECO-09-021510 KK 03SEP 09	LOC. I	SIZE A3	NUMERO (DWG NO) c-282332
D REVISED ET00-0121-04 A.V. 1995	REV. D1	FOGLIO (SHEET) 1	DI (OF) 1
A IN PRODUZIONE (I-3122) C. I. 1992			
REV. (REV. LTR.)	REVISIONI (REVISION RECORD)	DIS. (DR)	DATA (DATE)

DISTRIBUZIONE (PRINT DIST.)