






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	18NOV2023	NK	LET




RECOMMENDED PCB LAYOUT TOP VIEW
COMPONENT SIDE TOLERANCE ± 0.05 THICKNESS=3.0mm



	WAVE LENGTH (nm)		
	MIN.	AVG.	MAX.
GREEN	565	567	570
YELLOW	585	587	590

FORWARD VOLTAGE: $V_F=1.8-2.4V$
FORWARD CURRENT: $I_F=20mA$



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 18NOV2023 CHK N MANTIKOU 20NOV2023 APVD T LEININGER 20NOV2023		 TE Connectivity Ltd.	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± 0.15 4 PLC ± - ANGLES ± 2°		NAME RJ45 JACK THT 10/100 R/A LED 1X2 - -	
		PRODUCT SPEC 108-94945 APPLICATION SPEC 114-97854		SIZE A3	
MATERIAL 		FINISH 		CAGE CODE 00779	
		WEIGHT 7.36g		DRAWING NO C-2501552-4	
CUSTOMER DRAWING				RESTRICTED TO -	
				SCALE NTS	
				SHEET 1 OF 2	
				REV A1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—


NOTES: CONTINUATION FROM SHEET 1:

4 PROP 65 WARNING LABEL:

- THE WARNING LABEL ON THE PRODUCT OR LOWEST LEVEL PACKAGING
- CHEMICAL NAME: NICKEL (METALLIC)



WARNING: This product can expose you to chemicals including NICKEL (METALLIC) which is known to the state of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 18NOV2023	 TE Connectivity Ltd.			
		CHK N MANTIKOU 20NOV2023				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T LEININGER 20NOV2023	NAME RJ45 JACK THT 10/100 R/A LED 1X2			
	0 PLC ± —	PRODUCT SPEC 108-94945				
	1 PLC ± 0.35	APPLICATION SPEC 114-97854	SIZE A3	CAGE CODE 00779	DRAWING NO C-2501552-4	RESTRICTED TO —
MATERIAL 	2 PLC ± 0.25	WEIGHT 7.36g				
	3 PLC ± 0.15	CUSTOMER DRAWING		SCALE NTS	SHEET 2 OF 2	REV A1
	4 PLC ± —					
	ANGLES ± 2°					
	FINISH 					