






REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
C1		REDRAWN INTO CREO	27JUL2017	TS EC
D		REV PER ECO-17-011219	02AUG2017	TS EC




P1




P2



DIRECT ATTACH QSFP



△ LABEL INFORMATION: -1 SHOWN.




- SEE SHEET 2 FOR WIRING SCHEMATIC.
- PRODUCT AND PROCESSING MEETS THE REQUIREMENTS OF TE SPECIFICATION TEC-138-702.
- EEPROM DOES NOT INCLUDE PAGE SWAPPING.
- TEST IN ACCORDANCE WITH INFINIBAND EDR.

OBSOLETE		24	4000 +80/-0	1 2829040 0
OBSOLETE		24	3000 +80/-0	2829040 9
		26	3000 +80/-0	2829040-8
		26	2000 +80/-0	2829040-7
		30	2000 +80/-0	2829040-6
		30	1500 +50/-0	2829040-5
		30	1000 +50/-0	2829040-4
		30	500 +50/-0	2829040-3
		33	1000 +50/-0	2829040-2
		33	500 +50/-0	2829040-1
	HOT MELT CONFIGURATION	GAGE	"L" mm	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: T. SMITH 26JUL2017	TE Connectivity
mm	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	CHK: E. CUESTA 26JUL2017	
MATERIAL:	FINISH:	APVD: E. CUESTA 26JUL2017	NAME: CABLE ASSEMBLY, DIRECT ATTACH QSFP 28GIG INFINIBAND EDR
		PRODUCT SPEC:	SIZE: CAGE CODE: DRAWING NO: A100779C=2829040
		APPLICATION SPEC:	RESTRICTED TO:
		WEIGHT:	SCALE: 5:1 SHEET 1 OF 2 REV D
		CUSTOMER DRAWING	

REVISIONS				
P.	LTN.	DESCRIPTION	DATE	APVD.
		SEE SHEET 1		



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: T. SMITH 26 JUL 2017	
		CHK: E. CUESTA 26 JUL 2017	
DIMENSIONS: mm		APVD: E. CUESTA 26 JUL 2017	NAME: CABLE ASSEMBLY, DIRECT ATTACH QSFP 28GIG INFINIBAND EDR
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC	
		APPLICATION SPEC	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	SIZE: A1   CAGE CODE: 2829040   DRAWING NO: 2829040
CUSTOMER DRAWING		SCALE: 5:1	SHEET 2 OF 2   REV D