

4


3

2


1

LOC	DIST	REVISIONS				
		P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS
—	—		A	CREATION	05-Sep-14	JG
			B	UPDATED DRAWING	30-Jan-15	PG
			C	ECO-15-006767	19-May-15	JG


F
(No scale)
(Sans échelle)



Sliding
Couissant




Fixed
Fixe



Positionnement fourni par SIMEL sur demande.
Location is provided by SIMEL on request.


Fréquence nominale de l'AMORSIM : 1.83 Hz. ±0.2 Hz
Nominal frequency of the damper : 1.83 Hz. ±0.2 Hz

M12 Stainless steel bolts: 60Nm
Boulons M12 acier inoxydable: 60Nm




Soudé en usine
Factory welded

Soudé en usine
Factory welded



F

ITEM:

THIS DRAWING IS A CONTROLLED DOCUMENT. CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR TYCO ELECTRONICS CORPORATION IL EST SUSCEPTIBLE D'ÊTRE REVISÉ. POUR OBTENIR LA DERNIÈRE RÉVISION, CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS SIMEL SAS, 21220 GEVREY-CHAMBERTIN, FRANCE.		DWN /DESSINE GODARD	05-Sep-14	 TE connectivity SIMEL PRODUCTS		
DIMENSIONS: mm		CHK/VERIFIE -	-			
		APVD/APPROUVE -	-	NAME TITRE 5 AM 82 T250 F183		
		PRODUCT SPEC SPEC. PRODUIT 108-69090-001	-			
		APPLICATION SPEC SPEC. APPLICATION -	-			
MATERIAL MATIERE	-	FINISH FINITION	-	WEIGHT MASSE APPROX.	9.5 kg	SIZE FORMAT A3
CUSTOMER DRAWING		/PLAN CLIENT		UNIQUEMENT POUR REFERENCE	SCALE ECHELLE 1/4	SHEET FEUILLE 1 OF DE 1
				RESTRICTED TO RESERVE A -	REV C	