








P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	28AUG2023	NK	JDB
	F1	DRAWING RE-CREATED IN CREO	26DEC2023	NK	JDB



3D VIEW
SCALE 2:1



INSPECTION LEVEL 1: CONTROL CHART REQUIRED
(/1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
(72) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

1. COPLANARITY OF ALL CONTACTS AND CLIPS $\leq 0.1\text{mm}$

2 PART; 100 PCS. IN BUBBLE BAGS/BULK

 2				
1	-	-	TOP COVER	6
1	-	-	TRAY PACKAGING	5
1	1	-	SOLDER CLIP LEFT	4
1	1	-	SOLDER CLIP RIGHT	3
4	4	-	PINS	2
1	1	-	HOUSING	1
454829-E	254188-E	REV	DESCRIPTION	ITEM NO.
-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY		PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18AUG2023 N K NIKHIL CHK 20AUG2023 M SZELEG APVD 20AUG2023 J DE BRUJN		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mk ISO 80/15		NAME M12 MALE, A CODE, 4P, 17MM SMT	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781	
MATERIAL		FINISH		SIZE	RESTRICTED TO
-		-		A2	-
		WEIGHT		CAGE CODE	DRAWING NO
		-		00779	G=254188-E
CUSTOMER DRAWING				SCALE	SHEET
				5:1	1 of 1
				REV	F1