


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS


- NOTES:
- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH : MIN 2.0 µm BRIGHT TIN OVER MIN NICKEL UNDER PLATING.
 - PACKAGING: TUBE (WITH PICK AND PLACE CAP).
 - TOLERANCE NOT CUMULATIVE.
 - CUTTING BURR MAX. 0.25 mm.







48.0	50.0	25	2-2842129-5
46.0	48.0	24	2-2842129-4
44.0	46.0	23	2-2842129-3
42.0	44.0	22	2-2842129-2
40.0	42.0	21	2-2842129-1
38.0	40.0	20	2-2842129-0
36.0	38.0	19	1-2842129-9
34.0	36.0	18	1-2842129-8
32.0	34.0	17	1-2842129-7
30.0	32.0	16	1-2842129-6
28.0	30.0	15	1-2842129-5
26.0	28.0	14	1-2842129-4
24.0	26.0	13	1-2842129-3
22.0	24.0	12	1-2842129-2
20.0	22.0	11	1-2842129-1
18.0	20.0	10	1-2842129-0
16.0	18.0	9	2842129-9
14.0	16.0	8	2842129-8
12.0	14.0	7	2842129-7
10.0	12.0	6	2842129-6
8.0	10.0	5	2842129-5
6.0	8.0	4	2842129-4
DIM "F"	DIM "E"	POS. PER ROW	TE PN


1-2842129-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02AUG2019 SUBHASREE S		TE TE Connectivity						
		CHK 06AUG2019 KARTHIK JK								
		APVD 08AUG2019 PRASHANTH S								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.2 2 PLC ±0.15 3 PLC ±- 4 PLC ±- ANGLES ±2°		NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, VERTICAL, Sn, TUBE WITH PICK AND PLACE CAP						
	PRODUCT SPEC 108-64040									
	APPLICATION SPEC 114-32259									
	SIZE			CAGE CODE	DRAWING NO		RESTRICTED TO			
	WEIGHT -			A3	00779	C-2842129				
MATERIAL SEE NOTES		FINISH SEE NOTES		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV A1



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE