






REVISIONS				
P	LTN	DESCRIPTION	DATE	APPROV
1		PRELIMINARY	21JUL2016	TS GF
2		REV LABEL FORMAT	01SEP2016	TS GF
3		ADD NOTE 6	29NOV2016	TS GF

microQSFP
P1

QSFP28
P2



- CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFERENTIALLY)
 - CABLE ASSEMBLY TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.
 - PRODUCT AND PROCESSING MEETS THE REQUIREMENTS OF TE STANDARD TEC-138-702.
 - SEE SHEET 2 FOR WIRING SCHEMATIC.
- △ LABEL INFORMATION: -1 SHOWN



△ DUE TO SHORT CABLE LENGTH, THE PART NUMBERS INDICATED MAY NOT MEET IEEE802.3bJ RETURN LOSS AND MINIMUM INSERTION LOSS LIMITS.

4000±40	28 AWG	2821782-5
3000±40	28 AWG	2821782-4
2000±40	28 AWG	2821782-3
1000±40	28 AWG	2821782-2
500±25	28 AWG	2821782-1 △
L	WIRE GAGE	PART NO


THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL:		FINISH:	
mm	0 PLC	±					
	1 PLC	±					
	2 PLC	±					
	3 PLC	±					
	4 PLC	±					
	ANGLES	±					

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN T. SMITH 21JUL2016	G. FRANKLIN 21JUL2016	
	CHK G. FRANKLIN 21JUL2016	APPROV G. FRANKLIN 21JUL2016	
	PRODUCT SPEC	APPLICATION SPEC	
	SIZE	CAGE CODE	DRAWING NO
	A1	-	C=2821782
	WEIGHT		
	CUSTOMER DRAWING	SCALE 7:4	SHEET 1 OF 2 REV 3

REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
		SEE SHEET 1		



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 21JUL2016 CHK G. FRANKLIN 21JUL2016 APVD G. FRANKLIN 21JUL2016	TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME: CABLE ASSEMBLY microQSFP TO QSFP28 28 AWG
MATERIAL: -		WEIGHT: -		SIZE: A1 CAGE CODE: - DRAWING NO: C=2821782
CUSTOMER DRAWING		SCALE: 1:2		SHEET 2 OF 2 REV 3