



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS
	A2	ADDED POSITION 2 AND 3	11JUN2020	AY	PS
	A3	PARTS OBSOLESCENCE	23JUN2023	BGC	PS

NOTES:

- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.38 μ m GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 μ m BRIGHT TIN OVER NICKEL UNDER PLATING.
- PACKAGING: TUBE.
-  TOLERANCE NOT CUMULATIVE.
- CUTTING BURR MAX. 0.25 mm



1-2842151-0 AS SHOWN

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 08AUG2019

SUBHASREE S

CHK 13AUG2019

KARTHIK JK

APVD 14AUG2019

PRASHANTH S

PRODUCT SPEC

108-64040

APPLICATION SPEC

114-32259

WEIGHT

-

CUSTOMER DRAWING

NAME
AMPMODU 2mm BREAKAWAY HEADER,
DUAL ROW, RIGHT ANGLE, 0.38 Au, TUBE



SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=2842151 -


SCALE 5:1 SHEET 1 OF 1 REV A3

TE

TE Connectivity



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE