



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS
	A2	PARTS OBSOLESCENCE	22JUN2023	BGC	PS

NOTES:

- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.76 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 µm BRIGHT TIN OVER NICKEL UNDER PLATING.
- PACKAGING: TUBE (WITH PICK AND PLACE CAP).
- TOLERANCE NOT CUMULATIVE.
- CUTTING BURR MAX. 0.25 mm





OBSOLETE


1-2842156-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07AUG2019 SUBHASREE S	TE Connectivity		
		CHK 13AUG2019 KARTHIK JK			
		APVD 14AUG2019 PRASHANTH S			
		PRODUCT SPEC 108-64040			
DIMENSIONS: mm		APPLICATION SPEC 114-32259	NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, RIGHT ANGLE, 0.76 Au, TUBE, WITH PICK AND PLACE CAP		
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C=2842156
MATERIAL SEE NOTES		FINISH SEE NOTES	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV A2



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE