




SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN
(DIMENSIONS IN) mm

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

SCHEMA FORATURA CIRCUITO, SPESSORE 1.6±0.15
(PCB HOLE PATTERN THICKNESS 1.6±0.15) Ø3.2^{±0.1}

OBSOLETE	BIANCO (WHITE)	PBT NAT. (PBT UNFILLED)	282632 1
	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)

CUSTOMER DWG. FOR REFERENCE ONLY
DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED	RELEASE FOR PUBLICATION	19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)
(TOLERANCES: UNLESS OTHERWISE SPECIFIED)	—	—
± 0.3	2:1	



DESCRIZIONE (DESCRIPTION) 070 Sr. MULTILOCK* CONN. HEADER, 20 POSITION HORIZONTAL TYPE

LOC. SIZE	NUMERO (DWG NO)	REV.	FOGLIO (SHEET)
A3	C — 282632	B2	1 (OF) 4

REV.	REVISIONI (REVISION RECORD)	DIS.	DATA (DATE)
B2	REVISED PER ECN-23-205384	AP	31 MAR 2023
B1	REVISED PER ECN-22-133348	AP	10 JAN 2022
B	REVISED FOR ET00-0025-04	M.P.	23-2 '04
A3	ADDED NEW DASHES -2/-3/-4 (NOT YET RELEASED FOR PRODUCE.) WITH ECN ET00-0257-98	M.P.	29-7 '97
A2	REVISED FOR ET00-0352-97	M.P.	29-7 '97
A1	RELEASED FOR PROD.-1 ET00-0072-97 -1 IN PRODUZIONE CON ET00-0072-97	M.P.	27-2 '97
A	PRIMA EMISSIONE ET00-0049-96 FIRST ISSUE ET00-0049-96	M.P.	6-6 '96


CODICE FORNITORE "A 047"
(SUPPLIER CODE "A 047")

NUM. DI CAVITA' (CIRCUIT IDENTIF. NO.)


NO. IMPRONTA STAMPO (MOULD CAVITY IDENTIF. NO.)

- QUOTE MISURATE TRA I PIANI -X- E -Y-.
(DIMENSIONS MUST BE KEPT BETWEEN -X- AND -Y-).
- FORI PER DUE VITI AUTOFILETTANTI M3, DA APPLICARE PRIMA DELLA STAGNATURA AD ONDA.
(HOLES FOR TWO TAPPING SCREWS M3, BEFORE SOLDERING OPERATION).
- BLOCCHETTO ADATTO PER CONTROPARTE PLUG 20 VIE P/N 282369-1 E P/N 174952-1
(HOUSING SUITABLE FOR PLUG 20 POSITION P/N 282369-1 AND P/N 174952-1).
- TAB IN OTTONE STAGNATO
(TAB: BRASS TIN PLATED)

DISTRIBUZIONE
(PRINT DIST.)



12:33pm



DISTRIBUZIONE
(PRINT DIST.)

SCHEMA FORATURA CIRCUITO, SPESSORE 1.6±0.15
(PCB HOLE PATTERN THICKNESS 1.6±0.15)

GRIGIO (GREY)	PBT NAT. (PBT UNFILLED)	282632-4
FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)
(TOLERANCES: UNLESS OTHERWISE SPECIFIED)	-	-
ANGOLI (ANGLES)	± 0.3	SCALA (SCALE)
DIS. 19-FEB-96 (DR.) M. PALMA	DESCRIZIONE (DESCRIPTION) 070 Sr. MULTILOCK* CONN.	
CONT. 19-FEB-96 (CHK) C. TARDARI	HEADER, 20 POSITION HORIZONTAL TYPE	
APP. (REV.)	LOC. SIZE	NUMERO (DWG NO)
REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)	REV. FOGLIO (SHEET)
1	A3	C- 282632
2	B2	4 (OF) 4