



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS
	A2	PARTS OBSOLESCENCE	22JUN2023	BGC	PS

NOTES:


- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH : MIN 2.0 μm BRIGHT TIN OVER MIN NICKEL UNDER PLATING.
- PACKAGING: BULK PACK.
- TOLERANCE NOT CUMULATIVE.
- CUTTING BURR MAX. 0.25 mm





4:1


1-2842161-0 AS SHOWN

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASREE S 08AUG2019	TE Connectivity														
		CHK KARTHIK JK 13AUG2019															
		APVD PRASHANTH S 14AUG2019															
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, RIGHT ANGLE, Sn, BULK													
		0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±2°															
MATERIAL SEE NOTES		FINISH SEE NOTES		PRODUCT SPEC 108-64040		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
				APPLICATION SPEC 114-32259		A 3		00779		C=2842161		-					
				WEIGHT -		CUSTOMER DRAWING											
				SCALE				5:1		SHEET		1 OF 1		REV		A2	



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE