TÄ-Nr. Series 29 300AMP. POWER RELAY (28VDC)
SHORT FORM SIDE MOUNTING ENVIRONMENTALLY SEALED Page 1 of 2 0.079 MOUNTING DIMENSION 2.17+0.039 55+1 1.575 40 1.20 88a 0.21 1.02 M10 1.024 max. Torque 15-20Nm 26 M10 DIN 934 0.59 B10 DIN 137 **CIRCUIT** M4 ⁸⁸ o 88a 86 A1 SUPPRESSION DEVICE 3.94 100 **DIMENSIONAL TOLERANCES** 3 PLACE DECIMAL ± 0.010 2 PLACE DECIMAL ± 0.03 ANGULAR ± 0°30′ 57 40 \emptyset 1.969 ORDER-NO. ϕ 50 Third Angle Projection 29.312.02 WITHOUT SUPPRESSION 29.312.12 WITH SUPPRESSION

1996	Date	Name	Inch_	Scale	
Design	19.06.	Во	mm	1:1	
Check	19.06.	Grupp		eral Tolerances	
Appro			DIN 7168 m ISO 2768		



Drawing No. [≙] Order No. 29.312.02 29.312.12 TÄ-Nr.

300AMP. POWER RELAY (28VDC) ENVIRONMENTALLY SEALED

Series 29

Page 2 of 2

TECHNICAL DATA

ENVIRONMENTAL CHARACTERISTICS	
TEMPERATUR RANGE	-40° C TO +85° C (-40° F TO +185° F)
	50 000 FT
SEAL	IP67 (6 FEET / 0,2 BAR - 1MIN.) I.A.W. IEC 529
	IP6K9K (STEAM PRESSURE) DIN 40050 PART 9 AND I.A.W. IEC 529
SHOCK G-LEVEL	
VIBRATION	4 G / 50 - 2000 Hz
ELECTRICAL CHARACTERISTICS	
	100 MEGOHMS
AFTER LIFE OR ENVIRONMENTAL	
DIFLECTRIC WITHSTANDING VOLTAGE	SEA-LEVEL 1 MINUTE
DIEEEOTKIO WITHOTKINDING VOETKOE	SEA-LEVEL 1 MINUTE
MAX. CONTACT DROP INITIAL	0.15 VOLIS
	0.175 VOLTS
DUTY RATING	
RATED CONTACT LOAD (28 VDC)	
RESISTIVE LOAD	
INDUCTIVE LOAD	
MOTOR LOAD	
ENDURANCE	2 000 000 CYCLES
OPERATING CHARACTERISTICS	
COIL DATA	
VOLTAGE RANGE	
NOMINAL VOLTAGE	28 VDC
PICK UP VOLTAGE MAX	
	≤4 VDC FULL TEMP. RANGE
	0.4 AMP
COIL POWER APPROX	
TIME-MILLISECONDS-MAX.	
OPERATE	40
BOUNCE	5
RELEASE	
WEIGHT	
WIRE SECTION (AT NOMINAL LOAD)	MIN. 95 mm² / 0.147 sq. in. / AWG 0000
MOUNTING POSITION	OPTIONAL

SUBJECT TO CHANGE

	1996	Date	Name	Inch_	Scale	
	Design	19.06.	Во	mm		
	Check	19.06.	Grupp	General T		
1	Appro			DIN 7168 m ISO 2768		



Drawing No. - Order No.

29.312.02 29.312.12