

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		2011
© COPYRIGHT 2011		BY -		ALL RIGHTS RESERVED.
BLMC-16/70S-95R-MFX	2832281-1			
DESCRIPTION	PART NUMBER			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	CREATION	03AUG2017	LP	NA
	B	HEX BOLT HEAD REDUCED PER ECR	08SEP2020	NB	BM

D

C

C

B

A


D

C


C

B


A




⚠ - CONNECT ONLY WITH COPPER ROUND BAR : Ø12/14/16
- CONNECTER SEULEMENT SUR UNE BARRE RONDE CUIVRE : ...




TIGHTENING TORQUE : 15N.m
/COUPLE DE SERRAGE : ...



2 SHEAR POINTS



	AL				CU			
	ROUND STRANDED /Circ. câblé /RM	ROUND SOLID /Circ. massif /RE	SECTOR STRANDED /Sectoral câblé /SM	SECTOR SOLID /Sectoral massif /SE	ROUND STRANDED /Circ. câblé /RM	ROUND SOLID /Circ. massif /RE	SECTOR STRANDED /Sectoral câblé /SM	ROUND FLEXIBLE
CONDUCTOR CROSS-SECTION /Section conducteur /Querschnittsbereich mm ²	25-95	16-95	25-70 (95 with rounding)	50-95	10-95	10-50	25-70 (95 with rounding)	25-35 70
CONDUCTOR DIAMETER /Diamètre conducteur /Leiterdurchmesser mm	Ø 5.6-Ø 12.5	Ø 4.1-Ø 11	-	-	Ø 3.6-Ø 12.5	Ø 3.6-Ø 8	-	Ø 6.3-Ø 9.2 (25 ² -35 ²) Ø 11-Ø 12 (FOR 70 ²)



TOLERANCES UNLESS OTHERWISE SPECIFIED
TOLERANCES NON SPECIFIÉES: -

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. PETRIGNET CHK A. GUICHARD APVD N. ALMEIDA PRODUCT SPEC - APPLICATION SPEC IEC 61238-1 WEIGHT 124g CUSTOMER DRAWING	03AUG2017 TE Connectivity NAME BLMC-16/70S-95R-MFX - SIZE A3 CAGE CODE - DRAWING NO C-2832281 SCALE 1:1 SHEET 1 OF 1 REV B	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0 1 PLC ±0 2 PLC ±0 3 PLC ±0 4 PLC ±0 ANGLES ±0			
MATERIAL - ALU ALLOY	FINISH - TINNED			