




1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMO PLASTIC, COLOR BLACK.
PIN: COPPER ALLOY.
SOLDER NAIL: BRASS.
2. FINISH:
PIN: TIN PLATING OVER NICKEL PLATING OVERALL.
SOLDER NAIL: TIN PLATING OVER NICKEL PLATING OVERALL.
3. FINISH:
PIN: GOLD PLATING ON CONTACT AREA AND TIN PLATING ON
SOLDING AREA OVER NICKEL PLATING
SOLDER NAIL: TIN PLATING OVER NICKEL PLATING OVERALL.
4. PACKAGED IN TAPE AND REEL INSIDE OF CARTON.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECR-21-123282	07DEC2021	F.F	M.S
	B	ECR-22-131698	08MAR2022	F.F	M.S
	C	ECR-24-223672	14OCT2024	R.W	R.B
	C1	ECR-25-232616	18JAN2025	F.F	G.F




AS SHOWN: 1-2834465-2
1-2480474-2



52.50	48.30	44	4-2834499-4	4-2834465-4	4-2480474-4	4-2480475-4
48.90	44.70	40	4-2834499-0	4-2834465-0	4-2480474-0	4-2480475-0
45.30	41.10	36	3-2834499-6	3-2834465-6	3-2480474-6	3-2480475-6
41.70	37.50	32	3-2834499-2	3-2834465-2	3-2480474-2	3-2480475-2
38.10	33.90	28	2-2834499-8	2-2834465-8	2-2480474-8	2-2480475-8
34.50	30.30	24	2-2834499-4	2-2834465-4	2-2480474-4	2-2480475-4
30.90	26.70	20	2-2834499-0	2-2834465-0	2-2480474-0	2-2480475-0
27.30	23.10	16	1-2834499-6	1-2834465-6	1-2480474-6	1-2480475-6
23.70	19.50	12	1-2834499-2	1-2834465-2	1-2480474-2	1-2480475-2
DIMENSION B	DIMENSION A	POSITION	PN (Y KEY) TIN PLATING	PN (X KEY) TIN PLATING	PN (X KEY) GOLD PLATING	PN (Y KEY) GOLD PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 01MAR2021 FRANK FAN CHK: 01MAR2021 GEORGE FU APVD: 01MAR2021 MING SHI		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ± FINISH		NAME: MINIDYNAMIC HEADER 1.8 MM PITCH SMT TYPE	
		PRODUCT SPEC 108-137443		APPLICATION SPEC -	
MATERIAL - -		WEIGHT -		SIZE: A2 CAGE CODE: - DRAWING NO: C-2834465 RESTRICTED TO: -	
CUSTOMER DRAWING				SCALE: 4:1	SHEET 1 OF 4
				REV: C1	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			




3-2834465-2
3-2480474-2




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRANK FAN	01MAR2021	TE Connectivity				
		CHK GEORGE FU	01MAR2021					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±	APVD MING SHI	01MAR2021	NAME MINIDYNAMIC HEADER 1.8 MM PITCH SMT TYPE				
		PRODUCT SPEC 108-137443						
		APPLICATION SPEC -	SIZE A2	CAGE CODE -	DRAWING NO C=2834465	RESTRICTED TO -		
		MATERIAL - -	FINISH - -	WEIGHT -	CUSTOMER DRAWING			SCALE 4:1




printed on 20 Jan 2025 16:21 (China Standard Time) from TE310617




NOTES:
1 PLEASE REFER DIMENSIONS AND REQUIREMENTS IN SHEET1 AND SHEET2.



3-2834499-2
3-2480474-2



4-2834499-4	4-2834465-4	4-2480475-4	4-2480474-4	72	250	750
4-2834499-0	4-2834465-0	4-2480475-0	4-2480474-0	72	250	750
3-2834499-6	3-2834465-6	3-2480475-6	3-2480474-6	72	250	750
3-2834499-2	3-2834465-2	3-2480475-2	3-2480474-2	56	250	750
2-2834499-8	2-2834465-8	2-2480475-8	2-2480474-8	56	250	750
2-2834499-4	2-2834465-4	2-2480475-4	2-2480474-4	56	250	750
2-2834499-0	2-2834465-0	2-2480475-0	2-2480474-0	44	250	1000
1-2834499-6	1-2834465-6	1-2480475-6	1-2480474-6	44	250	1000
1-2834499-2	1-2834465-2	1-2480475-2	1-2480474-2	44	250	1000
PN (Y KEY) TIN PLATING	PN (X KEY) TIN PLATING	PN (X KEY) GOLD PLATING	PN (Y KEY) GOLD PLATING	TAPE WIDTH (MM)	QUANTITY PER REEL /PCS	QUANTITY PER CARTON /PCS

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 01MAR2021 FRANK FAN		 TE Connectivity								
			CHK 01MAR2021 GEORGE FU										
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 01MAR2021 MING SHI		NAME MINIDYNAMIC HEADER 1.8 MM PITCH SMT TYPE							
		0 PLC ±-		PRODUCT SPEC									
		1 PLC ±-		108-137443									
		2 PLC ±0.25		APPLICATION SPEC									
		3 PLC ±-		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
		4 PLC ±-		-									
MATERIAL		FINISH		WEIGHT		A2		-		C-2834465		-	
-		-		-		CUSTOMER DRAWING		SCALE 4:1		SHEET 4 OF 4		REV C1	
-		-											