

REVISIONS

REV	DESCRIPTION /MODIFICATIONS	DATE	DWN	APVD
1	NEW DRAWING	06APR2020		GS

NOTES

1. ALL DIMENSIONS ARE IN INCHES  
MILLIMETERS

2. DIMENSIONS APPEARING IN TABLE



ARE AS FALLOWS :

a- AS SUPPLIED


b- AFTER UNRESTRICTED RECOVERY

3. TUBING MATERIAL PER RK-6008/2

4. PART NUMBERING SYSTEM



AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS


Part Description	H		P MIN b	W ±20% b
	MIN a	MAX b		
RT-1116-TW-1.50-3/225-0	1.40 / [35.6]	.75 / [19.1]	3.00 / [76.2]	.40 / [1.02]

ADHESIVE SPECIFICATION REFERENCE

Adhesive slash number	Adhesive Type	Adhesive Specification
/225	S-1206	RW-2074

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS :  
mm



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

DWM

CHK GREG S

APVD GREG S

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME  
DR-25 TUBING

SIZE  
FORMAT  
A3

CAGE CODE

DRAWING NO  
EPD-202-32011-01

RESTRICTED TO

SCALE NTS

SHEET 1 OF 2

REV 1