



| LOC | DIST | REV | ZONE | LTR | DESCRIPTION              | DATE    | APPD |
|-----|------|-----|------|-----|--------------------------|---------|------|
| G   | 14   | P   |      | A   | REVISED PER 0720-0230-93 | 2/28/94 | DAF  |

METRIC

DIMENSIONS LISTED IN mm [ INCHES ]

|                    |                        |
|--------------------|------------------------|
| AMP                | IL E13288 Listed       |
| WIRE RANGE         |                        |
| 22-16 AWG STRANDED | 22-16 AWG STRANDED     |
| LR7189 Certified   | MILITARY P/N AND CLASS |
| NOT CERTIFIED      | NOT APPLICABLE         |



STAMP AMP 22-18\* APPROX AS SHOWN  
22-16 TERMINALS ARE STAMPED 22-18 IN  
ACCORDANCE WITH MILITARY SPECIFICATION  
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16

AMP INCORPORATED  
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING  
TEMPERATURE:  
170°C MAX

FOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTS  
1-800-522-6752

FOR APPLICATION  
TOOLING INFORMATION  
1-800-722-1111

FOR ORDER ENTRY  
1-800-526-5142

VOLTAGE RATING:  
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:  
0.26-1.65mm² [509-3.260] CIR MILS  
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE COMPANY ASSUMES NO LIABILITY FOR  
REVISIONS.

DO NOT SCALE PRINT.  
UNLESS SPECIFIED  
DIMENSIONS IN mm - FINEST  
TOLERANCES ON:  
2 PLG DEC ±  
3 PLG DEC ±  
ANGLES ±

MATERIAL  
COPPER PER  
ASTM B-152  
ANNEALED

FINISH  
TIN PLATE  
0.00254 [1.000100] MIN  
THK PER MIL-T-10727

DR 2-23-93  
TA BRINKMAN  
CHK 2-23-93  
DA PATTERSON  
APPD 2-23-93  
DE MILLER  
APPD 2-23-93  
JL NECKLEY  
PRODUCT SPEC

AMP  
AMP Incorporated  
Harrisburg, PA 17105-3608

TERMINAL, SLOTTED  
RING TONGUE, BUDGET

APPLICATION SPEC  
WEIGHT -

SIZE  
CAGE CODE  
00779  
DRAWING NO  
323838

SCALE 10:1

SHEET 1 OF 1

323838  
PART NO

323838