



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS
	A2	ADDED POSITION 2 AND 3	11JUN2020	AY	PS

NOTES:


- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH : MIN 2.0 μ m BRIGHT TIN OVER MIN NICKEL UNDER PLATING.
- PACKAGING: TUBE.
- TOLERANCE NOT CUMULATIVE.
- CUTTING BURR MAX. 0.25 mm





48.0	50.0	25	2-2842149-5
46.0	48.0	24	2-2842149-4
44.0	46.0	23	2-2842149-3
42.0	44.0	22	2-2842149-2
40.0	42.0	21	2-2842149-1
38.0	40.0	20	2-2842149-0
36.0	38.0	19	1-2842149-9
34.0	36.0	18	1-2842149-8
32.0	34.0	17	1-2842149-7
30.0	32.0	16	1-2842149-6
28.0	30.0	15	1-2842149-5
26.0	28.0	14	1-2842149-4
24.0	26.0	13	1-2842149-3
22.0	24.0	12	1-2842149-2
20.0	22.0	11	1-2842149-1
18.0	20.0	10	1-2842149-0
16.0	18.0	9	2842149-9
14.0	16.0	8	2842149-8
12.0	14.0	7	2842149-7
10.0	12.0	6	2842149-6
8.0	10.0	5	2842149-5
6.0	8.0	4	2842149-4
4.0	6.0	3	2842149-3
2.0	4.0	2	2842149-2


1-2842149-0 AS SHOWN

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07AUG2019 SUBHASREE S	 TE Connectivity		
		CHK 13AUG2019 KARTHIK JK			
		APVD 14AUG2019 PRASHANTH S			
		PRODUCT SPEC 108-64040			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, RIGHT ANGLE, Sn, TUBE		
		0 PLC $\pm$ 1 PLC ± 0.2 2 PLC ± 0.15 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm 2^\circ$	APPLICATION SPEC 114-32259		
		FINISH SEE NOTES	WEIGHT -		
MATERIAL SEE NOTES		CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779
				DRAWING NO C-2842149	RESTRICTED TO -
				SCALE 5:1	SHEET 1 OF 1
				REV A2	



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE