



P	LTR	DESCRIPTION	DATE	DWN	APVD
	N2	REVISE PER ECN-25-330062	01JUL2025	ED	WZ



- ① BRASS PER QQ-B-626.
- ② SILVER PLATE PER QQ-S-365, 5.08 μ m[.000200] MINIMUM THICK.
- ③ NICKEL PLATE PER QQ-N-290, 2.54 μ m[.000100] MINIMUM THICK.
- ④ $\varnothing 0.79 \pm 0.08$ [.031 $\pm$.003] (3 HOLES) 120° APART.
- ⑤ GOLD PLATE PER MIL-G-45204, 0.51 μ m[.000020] MINIMUM THICK.
- ⑥ SILVER PLATE PER QQ-S-365, 2.54 μ m[.000100] MINIMUM THICK.
- ⑦ 10PCS PER LABELED BAG, 100 BAGS PER LABELED INNER CARTON(1000) AND 10 INNER CARTONS(10000) PER SHIP BOX.

⑦	2.39 $\pm$ 0.15 [.094 $\pm$.006]	14.10 $\pm$ 0.25 [.555 $\pm$.010]		③	①	9-329631-3
	2.77 [.109]	15.88 [.625]		②	①	9-329631-2
	2.39 $\pm$ 0.15 [.094 $\pm$.006]	14.10 $\pm$ 0.25 [.555 $\pm$.010]	④	⑥	①	9-329631-1
	2.39 $\pm$ 0.15 [.094 $\pm$.006]	14.10 $\pm$ 0.25 [.555 $\pm$.010]		⑥	①	9-329631-0
	2.77 [.109]	15.88 [.625]		⑤	①	2-329631-2
	2.39 $\pm$ 0.15 [.094 $\pm$.006]	14.10 $\pm$ 0.25 [.555 $\pm$.010]		③	①	2-329631-1
	2.77 [.109]	15.88 [.625]		③	①	2-329631-0
	2.77 [.109]	15.88 [.625]		②	①	1-329631-9
	2.39 $\pm$ 0.15 [.094 $\pm$.006]	14.10 $\pm$ 0.25 [.555 $\pm$.010]	④	⑥	①	1-329631-7
	2.39 $\pm$ 0.15 [.094 $\pm$.006]	14.10 $\pm$ 0.25 [.555 $\pm$.010]		③	①	1-329631-2
	2.39 $\pm$ 0.15 [.094 $\pm$.006]	14.10 $\pm$ 0.25 [.555 $\pm$.010]		⑥	①	329631
	B	A	HOLES	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	P. ALSEDEK	16MAY90
CHK	R.E. RUTH	06SEP90
APVD	M. PHILLIPS	20SEP90
PRODUCT SPEC		
APPLICATION SPEC		



TE Connectivity

NAME				JAM NUT	
				-	
SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
A3	00779	C-329631		-	
CUSTOMER DRAWING			SCALE	SHEET	REV
			4:1	1 of 1	N2

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC $\pm$ -
	1 PLC $\pm$ -
	2 PLC $\pm$ 0.13 [.005]
	3 PLC $\pm$ -
	4 PLC $\pm$ -
MATERIAL	FINISH
⑦	⑦ & ⑦