




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REDRAWN (ECR-15-004409)	19MAR2015	M.G.	M.G.
	A5	REVISED AS PER ECN-24-296301	03DEC2024	V.N.	V.N.
	A6	REVISED AS PER ECN-25-314634	09APR2025	V.N.	V.N.

D

C


B

A



- NOTE
- 1 SHELL 40 POS. IN PA6.6 GLASS FILLED FOR COLOR SEE TABLE TO SHEET 2/3
 - 2 LEVER IN PA6.6 GLASS FILLED COLOR RED
 - 3) THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION
 - 4) N°1 SHELL + N°2 HOUSINGS ARE SUPPLIED IN KIT ACCORDING TO TABLE SHEET 2/3 WITH EQUIVALENT NUMBER OF PIECES FOR EACH COMPONENT IN A BOX

P/N 284229-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O.CANUTO CHK A.GENTA APVD A.BRUNI PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	22SEPT1998 22SEPT1998 22SEPT1998	 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±2° FINISH		NAME MQS 20+20 POS. FRAME ASSY (KIT)	
				SIZE A2	CAGE CODE 00779
MATERIAL - SEE NOTES				DRAWING NO C=284229	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 3:1	SHEET 1 OF 3
				REV A6	

D



C

B

A

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

P/N	CODING KEY DETAIL	COLOUR	HOUSING P/N	COUNTERPART
284229-1		BLACK	284150-1 (1x)	114-20202 COD. I
			284150-2 (1x)	
284229-2		BLUE	284150-3 (1x)	114-20202 COD. IV
			284150-4 (1x)	

5) FOR HOUSING DETAILS SEE SHEET 3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O.CANUTO 22SEPT1998	TE Connectivity						
		CHK A.GENTA 22SEPT1998							
DIMENSIONS: mm		APVD A.BRUNI 22SEPT1998	NAME MQS 20+20 POS. FRAME ASSY (KIT)						
		PRODUCT SPEC -							
		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL -		WEIGHT -	A2	00779	C=284229	-			
CUSTOMER DRAWING			SCALE		3:1	SHEET	2 OF 3	REV	A6

