




28APR2025	 TE Connectivity				
28APR2025					
28APR2025	NAME JACK, BHD, DUAL CRIMP, BNC				
SON	-				
SPEC	-				
ION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-	A2	00779	C-331693	-	
ER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV W




RECOMMENDED STRIP LENGTH



SUGGESTED PANEL CUTOUT

1. MAX PANEL THICKNESS: 6.10 [.240]
2. SEE INSTRUCTION SHEET 408-1914-3
3. PARTS PACKAGED UNASSEMBLED

69478-1		00779 M39012/19B0003 YY WW		RG58/U, 58A/U, 58B/U, 58C/U		1-331693-1	
USE CRIMPING TOOL		STAMPING		FOR USE WITH CABLE		ASSEMBLY NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L. PROSPER 28APR2025 CHK J. SLUSSER 28APR2025 APVD D. WILSON 28APR2025  TE Connectivity			
DIMENSIONS: mm [in]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME JACK, BHD, DUAL CRIMP, BNC			
		0 PLC ±.		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		1 PLC ±.					
		2 PLC ±.					
3 PLC ±.41 [.016]		PRODUCT SPEC -		A2 00779 C=331693 -			
4 PLC ±.		APPLICATION SPEC -					
ANGLES ±.		FINISH		WEIGHT -			
MATERIAL				CUSTOMER DRAWING			
-	-	-		SCALE 4:1 SHEET 1 OF 1 REV W			
-	-	-					