



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H3	REVISED PER ECR-25-232847	26MAR2025	SA	DSC



AMP WIRE RANGE	E13288 Listed
6 AWG SOLID OR STRANDED	6 AWG STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
6 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 6* APPROX AS SHOWN
- 2 COPPER PER ASTM B152, ANNEALED
- 3 FINISH: TIN PLATE 0.00254[.00010] MIN EXT THK PER ASTM B545
4. BODY MATERIAL THK: 1.448±0.051[.057±.002]



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C[338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 10.5-16.8mm ² [20,800-33,100] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-24-93	750		TAPE & REEL	2-33464-2
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 3-24-93	100		LOOSE PIECE	33464
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DE MILLER 3-24-93	QUANTITY		PACKAGE TYPE	PART NO
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC UL 486 A-B APPLICATION SPEC	NAME TE Connectivity			
MATERIAL		WEIGHT	SIZE A2		CAGE CODE 00779	DRAWING NO C-33464
FINISH		CUSTOMER DRAWING	RESTRICTED TO -		SCALE 4:1	
2		3	SHEET 1 OF 1		REV H3	