SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA C22.2 No. 8 VDE APPROVED: EN 60939-2

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 30 AMP 277 VAC LINE TO GROUND

AND 480VAC PHASE TO PHASE

50

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT.

EACH LINE TO GROUND: 8.7 mA @ 277VAC 50 HZ

OPERATING AMBIENT TEMP. RANGE: -10°C TO +50°C @ RATED CURRENT, In. IN AN AMBIENT, T_0 , HIGHER THAN 50°C, THE MAXIMUM OPERATING CURRENT, I_0 , IS AS FOLLOWS: $I_1 = I_2 - \sqrt{100 - T_0}$ $I_0 = I_r -$ <u> 100 - Ta</u>

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 50°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOMER DRAWING CATALOG # 30BCF10R APPRVD DATE ECN# 15-0153<u>24</u> 200CT15 HS

TEST SPECIFICATIONS:

INDUCTANCE: 1.60 mH NOMINAL CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: 0.1 μF±20% LINE TO LINE: 4.95 μF±20%


DISCHARGE RESISTOR: 1.5 / .66 M \(\triangle \triangle L/\triangle \triangle AND L/\triangle I.R. NO DISCHARGE RESISTOR: 6000M₁ (MIN.) 100VDC, 20°C AND 50% RH@

RECOMMENDED RECEIVING INSPECTION HIPOT:

1850 VDC FOR 1 MINUTE LINE TO LINE: 1850 VDC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50 A - 50 A (TYPICAL) INSERTION LOSS												
FREQUENCY MHz	.01	.03	.05	.10	.15	.30	.50	1.0	3.0	5.0	10	30
COMMON dB	1	11	19	30	38	54	58	61	71	54	39	20
DIFF. dB	23	31	29	49	62	87	84	78	68	62	59	46
SHEET SIZE	THIRD A	NGLE PRO	5)	THIS INFORMATION IS COMPIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS COMPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCUSSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS COMPORATION.								

UNLESS OTHERWISE SPECIFIED
TOLERANCE TO BE ±0.64 (±0.025)
MATERIAL & FINISH: AS SUPPLIED
DIMENSIONS IN MM (INCHES) NOTES:

30BCF10R-A.ckd

TE Connectivity

CUSTOMER DRAWING

TE PART ND.: 2-1609989-2

DRAWTNG NUMBER NTS 300CT15 30BCF10R A