






A STAMP AMP 16-14HD* APPROX AS SHOWN

AMP WIRE RANGE		UL E13288 Listed	
16-14HD AWG STRANDED		16-14HD AWG STRANDED	
UL LR7189 Certified		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
1.04-2.62mm² [2,050-5,180] CIR MILS
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -
MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH TIN PLATE
0.00254L.0001001 MIN
THK PER MIL-T-10727

DR 2-1-93
TA BRINKMAN
CHK 2-1-93
DA PATTERSON
APPD 2-1-93
DE MILLER
APPD 2-1-93
JL HECKLEY
PRODUCT SPEC



AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE,
HEAVY DUTY, BUDGET

APPLICATION SPEC
WEIGHT -

SIZE CAGE CODE DRAWING NO
G 00779 G=34968
SCALE 8:1 SHEET 1 OF 1

34968
PART NO