


Technical Data

Case Material:	Cover	Vyncolit black
	Base Plate	PA GF black
Switch Lever Material		PA GF red
Min. Insulation Resistance		100 MOhm
Dielectric Withstanding Voltage		1050V-1min.
Max. Contact Drop during Resistive Load		150mV
Voltage		to 32 VDC
Duty Rating		2x500A
Overload		2x2000A-1.5min.
		2x2500A-10sec.
Sealing		IP 67 / IEC 529
Vibration		10G,18-500Hz
Shock G-Level		50G,11ms
Duty Shock-6000 Zyklen		40G,6ms
Weight		ca. 650g
Temperature Range		-40°C to +85°C
Wire Section (at nominal Load)		min.250mm ²
Mounting position		optional
Switch lever		not removeable
Max. Torque (Main Contacts)		18-22 Nm

	Date	Name	mm	Scale
Drawn	12.11.2015	Seege		1:2
Check	12.11.2015	Grind	General Tolerances DIN ISO 2768 cL	



Drawing No:	35-524-241-R-900
NSN:	