




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		AB		REVISED PER ECR-12-013323	09AUG12	KH	TM




- 1 PLATED WITH 0.00076 [.000030] GOLD, OVER 0.00127 [.000050] NICKEL UNDERPLATE.
- 2 PLATED INTERNALLY WITH 0.00076 [.000030] GOLD.
- 3 WIRE RANGE 0.2-0.75 mm<sup>2</sup> (24-18 AWG).
- 4 INSULATION RANGE 1.02-2.54 [.040 -.100] DIA.



DETAIL A  
SCALE 20:1



SECTION A-A  
SCALE 10:1



SECTION B-B  
SCALE 10:1

350706-7	0.30[.012] BRASS	GOLD 1	350699-7
-	0.30[.012] PH BRZ	PRE-TIN	350699-3
350706-2	0.30[.012] BRASS	GOLD 1 2	350699-2
350706-1	0.30[.012] BRASS	PRE-TIN	350699-1
LOOSE PIECE (REF)	MATERIAL	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25-FEB-2002 K. WHITAKER	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK 25-FEB-2002 S. RIDGILL		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 25-FEB-2002 S. RIDGILL	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	SPLIT PIN, UNIVERSAL MATE-N-LOK™	
MATERIAL SEE TABLE		APPLICATION SPEC	SIZE	CAGE CODE
FINISH SEE TABLE		WEIGHT -	A2	00779
		CUSTOMER DRAWING	DRAWING NO	RESTRICTED TO
		SCALE 4:1	C=350699	-
		SHEET 1 of 1	REV AB	