










REVISIONS					
P	LTN	DESCRIPTION	DATE	DWN	APVD
AA5		REVISED PER ECR-20-100517	08OCT2020	PC	JS
AB		REVISED PER ECR-24-218682	09SEP2024	AK	BR

- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK CAP OR HEADER.
 - SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS (1.0) LBS. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS (.5) LBS.
 - DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- 4 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 5 NOT MANUFACTURED IN THE UNITED STATES.
- 6 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE ON EACH SIDE OF HOUSING.
- NYLON, UL94V-0.



DETAIL A
SCALE 6:1
OPTIONAL CONSTRUCTION



BLACK	1-350720-9
GRAY	1-350720-8
BLUE	1-350720-6
GREEN	1-350720-5
YELLOW	1-350720-4
ORANGE	1-350720-3
RED	1-350720-2
BROWN	1-350720-1
5 NATURAL	350720-4
NATURAL	350720-1
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HAMM 07JUN2001	
DIMENSIONS: mm [INCHES]		CHK S. RIDGILL 07JUN2001	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. RIDGILL 07JUN2001	NAME PLUG, 9 CIRCUIT, UNIVERSAL MATE-N-LOK
0 PLC ±	1 PLC ±	PRODUCT SPEC	SIZE
2 PLC ±0.13 [1.005]	3 PLC ±	APPLICATION SPEC	CAGE CODE
4 PLC ±	ANGLES ±30°	WEIGHT	DRAWING NO
MATERIAL		CUSTOMER DRAWING	RESTRICTED TO
FINISH		A 00779 ©=350720	SCALE 4:1 SHEET 1 OF 1 REV AB