
		REVISIONS						
ŀ	Р	LTR	DESCRIPTION	DATE	DWN	APVD		
		Т	PRODUCTION ISSUE	29JAN2019	PNT	MT		






TABLE OF DIMENSIONS										
PART	H & J		К		Р	R	S	Т	HW & JW	KW
NUMBER	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±20%	±20%
	а	b	а	b	b	b	b	b	b	b
322A112	13.2 [.52]	5.8 [.23]	6.6 [.26]	3.0 [.12]	52.3 [2.06]	26.2 [1.03]	19.3 [.76]	N/A	1.52 [.06]	1.02 [.04]
322A123	26.9 [1.06]	12.4 [.49]	6.6 [.26]	3.0 [.12]	83.3 [3.28]	41.7 [1.64]	<u>27.2</u> [1.07]	10.7 [.42]	2.54 [.10]	1.02
322A134	<u>26.9</u> [1.06]	12.7 [.50]	13.2 [.52]	5.8 [.23]	107.7 [4.24]	53.8 [2.12]	38.6 [1.52]	20.3 [.80]	2.54 [.10]	1.52 [.06]
322A148	55.6 [2.19]	<u>25.4</u> [1.00]	13.2 [.52]	<u>5.8</u> [.23]	180.6 [7.11]	90.4	57.4 [2.26]	25.4 [1.00]	4.57 [.18]	1.52 [.06]
322A158	55.6 [2.19]	<u>25.4</u> [1.00]	<u>26.9</u> [1.06]	12.4 [.49]	222.3 [8.75]	111.3 [4.38]	77.7 [3.06]	38.1 [1.50]	4.57 [.18]	2.54 [.10]

DIMENSIONS:	DWN 29JAN2019 PRAVEEN N T	MATERIAL SEE SHEET 2	FINISH -		
mm [INCHES] TOLERANCES UNLESS	CHK 29JAN2019 N NAGAR				
OTHERWISE SPECIFIED:	APVD 29JAN2019 M TAYLOR	TE Connectivity Ltd.			
0 PLC ± - 1 PLC ± - 2 PLC ± -	PRODUCT SPEC —	TRANSITION, 90 DEG. SIDE BREAKOUT			
3 PLC ± -	APPLICATION SPEC				
4 PLC ± – ANGLES ± –	_	SIZE CAGE CODE DRAWING NO	RESTRICTED TO		
	WEIGHT	A4 00779 C- 322A1	12-XX-0THRU158-XX-0		
	CUSTOMER DRAWING	S	CALE DNS SHEET 1 OF 2 REV T		

ALL RIGHTS RESERVED.

TE Connectivity Ltd.

COPYRIGHT

DNS

OF 2

CUSTOMER DRAWING