

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


LOC F DIST 00

REVISIONS

© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
F		NEW P/N 336587-2 (SILVER PLATED VERSION)	20NOV2013	NT.N	JL
G		ADDED THE FORCE VALUES OF P/N 336587-2	14MAY2014	NT.N	JL
H		INSERT. AND EXTRACT. FORCES CHANGED	05FEB2015	NT.N	JL
J		UPDATED TE LOGO WITH 2 ALTERN. MARKINGS	07APR2015	NT.N	JL

ALL DIMENSIONS MEASURED WITH A GAUGE REF. 1.6±0.02(THK) AND 3.0±0.02





1. FOR P.C. BOARD 1.6mm THK.  
 CUTOUT 3.0±0.1x7.0±0.1mm  
 DELIVERING: IN REEL STRIP VERSION  
 STRIP FEED: 6.0±0.08  
 MATERIAL: PHOSPH BZ ACCORDING TO UNS C51100  
 TEMPER: H04  
 MATERIAL: THK 0.32±0.02  
 USE STEEL GAUGE 965850-1

PART NUMBER	FIRST INSERTION	FIRST EXTRACTION
336587-1 (PRE TIN PLATED)	MIN.16 N	MIN.3 N
	MAX.32 N	MAX. 13 N (H)
336587-2 (PRE SILVER PLATED)	MIN.20 N (H)	MIN.11 N
	MAX.35 N	MAX.20 N


△ TE LOGO IN THIS AREA WITH 2 ALTERNATIVE MARKINGS (J)

F CONTACT ON REEL IN FREE POSITION FOR INFORMATION ONLY

SCALE 5:1



TE LOGO WITH 2 ALTERNATIVE MARKINGS (J)



F	PRE-SILVER PLATED 2 - 4µm OVER 1 - 2µm NICKEL	PHOSPHOR BRONZE	336587-2
F	PRE-TIN PLATED 1 - 3µm	PHOSPHOR BRONZE	336587-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 20FEB2001 F.J.CARBONELL

CHK 20FEB2001 J.LAZARO

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

Customer Drawing

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±0.3
1 PLC	±0.3
2 PLC	±0.3
3 PLC	±0.3
4 PLC	±0.3
ANGLES	±1°
MATERIAL	FINISH



TERMINAL RECEPT. PARA C.IMPRESO 1.6mm TERMINAL RECEPT FOR P.C.B 1.6mm

SIZE A3 CAGE CODE 00779 DRAWING NO C-336587 RESTRICTED TO -

SCALE 3:1 SHEET 1 OF 1 REV J