

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20






© COPYRIGHT 20

BY -






ALL RIGHTS RESERVED.

REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	14MAR'07	SC	JK
	B	REVISED PER ECR-09-011788	25MAY'09	SC	JK
	C	REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z
	C1	ECR-25-247422	25JUN2025	KD	D,Z

- 1 THIS HOUSING ACCEPTS TAB TERMINAL:
-TAB CONTACT: 177917- (AWG#16-#20)
177916- (AWG#22-#26)
- 2 MATING CONN. P/N
-PLUG HSG: 368576-
-REC CONTACT: 177915- (AWG#16-#20)
177914- (AWG#22-#26)
- 3 APPLICABLE DOUBLE LOCK PLATE: 177919-1
* IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y

- 4 GENERAL TOLERANCES: ± 0.3
- 5 APPLICABLE PANEL THICKNESS: 0.8~2.0 (SEE FIG.1)
- 6 INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
- 7 EDGE OF THICKNESS MAY MUST DOT ROUND FOR MOLDED PANEL.
- 8 MATERIAL: PA66,UL94V-0
COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF
NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING
CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)



BLUE	368588-6
YELLOW	368588-4
NATURAL	368588-1
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SC KIM	 TE Connectivity			
DIMENSIONS: mm		CHK BW KANG				
		APVD JK SONG				
		PRODUCT SPEC 108-5410				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC \pm 1 PLC \pm 2 PLC \pm 3 PLC \pm 4 PLC \pm ANGLES \pm FINISH \pm		APPLICATION SPEC 114-5175	NAME PDL 6P CAP HSG 3.96mm D/R P/M (GWT)			
MATERIAL 		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-368588	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 3:1	SHEET 1 OF 1	REV C1	