


Circuit



In Entwicklung

Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF red
Min.Insulation Resistance	100M0hm
Dielectric Withstanding Voltage	1050V-1min.
Max.Contact Drop during Resistive Load	150mV
Voltage	up to 32VDC
Duty Rating	250A
Overload	500A-180sec.
	1000A-30sec.
Sealing	IP 67/ IEC 529
Vibration	4G/ 50-2000Hz
Shock G-Lever	6G/ 11ms
Weight	~205g / 0.45 pound
Temperature Range	-40°C to +85°C
Wire Section (At Nominal Load)	min. 70mm ²
Mounting Position	optional
Switch Lever	not removeable
Torque (Main Terminals)	15-20Nm

For this drawing we reserve the copyright in accordance with DIN ISO 16016

	Date	Name
Create	11.02.2020	Seege
Edited	11.02.2020	Seege
Check	11.02.2020	Grind

mm ↔	Scale 1:2
General Tolerances	



Drawing No:

35-211-151-R

NSN: