



Technical Data:

Case Material .....	PA GF black
Switch Lever Material .....	PA GF red
Min.Insulation Resistance .....	100M0hm
Dielectric Withstanding Voltage .....	1050V-1min.
Max.Contact Drop during Resistive Load .....	150mV
Voltage .....	up to 32VDC
Duty Rating .....	2x 200A
Overload .....	2x 500A-180sec.
.....	2x 1000A-30sec.
Sealing .....	IP 67/ IEC 529
Vibration .....	4G/ 50-2000Hz
Shock G-Lever .....	6G/ 11ms
Weight .....	~310g / 0.68 pound
Temperature Range .....	-40°C to +85°C
Wire Section (At Nominal Load) .....	min. 70mm <sup>2</sup>
Mounting Position .....	optional
Switch Lever .....	removeable
Torque (Main Terminals) .....	12-13Nm

Für diese Zeichnung behalten wir uns das Urheberrecht gemäß DIN ISO 16016 vor

	Datum	Name	Allgemeintoleranz	Maßstab		Zeichnungs-Nr.:
Erstel.	04.05.2016	NMiel	DIN ISO 2768 cL	1:2		35-220-000-R
Bearb.	05.12.2019	Seege				
Freig.	09.03.2020	Grind				Vers.Nr.: