

# 3EHQ8 & 3EHQ8M

## SAFETY ORGANIZATION(S):

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET.

UL RECOGNIZED  
CSA CERTIFIED  
VDE APPROVED  
SEV APPROVAL PENDING

UL 544  
CSA 22.2, NO.0,0.4,8  
VDE 565-3

## OPERATING SPECIFICATIONS:

LINE VOLTAGE/CURRENT, 3 AMP, 120/250 VAC  
2 AMP./40°C, 250 VAC  
LINE FREQUENCY, 50-60Hz

MAX. LEAKAGE CURRENT, EACH, 2 µA at 120V 60Hz  
LINE TO GROUND, 5 µA at 250V 50Hz

OPERATING AMBIENT TEMP. RANGE, -10°C TO +40°C @ RATED CURRENT,  $I_r$

IN AN AMBIENT,  $T_a$ , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT,  $I_o$ , IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{85 - T_a}{45}}$$

## RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE, -40°C TO +85°C  
HUMIDITY, 21 DAYS @ 40°C 95% RH  
CURRENT OVERLOAD TEST, 6 TIMES RATED CURRENT FOR 8 SECONDS

## TEST SPECIFICATIONS:

INDUCTANCE, 32.18 mH NOMINAL  
CAPACITANCE, MEASURED @ 1 KHz, 0.25VAC MAX., 25°C±1°C

LINE TO LINE, .94 µF ±20%  
DISCHARGE RESISTOR, 270KΩ


LINE/GROUND AND LINE/LINE, 6000MΩ (MIN) AT 100VDC  
INSULATION RESISTANCE, 20°C AND 50% RH

## RECOMMENDED RECEIVING INSPECTION HIPOT:

LINES TO GROUND, 2250 VDC FOR 1 MINUTE  
LINE TO LINE, 1450 VDC FOR 1 MINUTE

## FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



## 50n - 50n (MINIMUM) INSERTION LOSS

FREQUENCY MHz	.01	.015	.02	.05	.15	.5	1	2	5	10	20	30
COMMON dB	19	22	24	32	44	44	40	38	28	22	13	10
DIFF. dB	1	2	18	43	68	75	75	72	70	65	62	60

UNLESS OTHERWISE SPECIFIED,  
TOLERANCE TO BE ±.025

MATERIAL & FINISH, AS SUPPLIED

This document is proprietary to CORCOM INC. and is not to be reproduced nor used for manufacturing purposes except on CORCOM'S prior written consent.

**corcom**  
LIBERTYVILLE, IL 60048

POWER LINE FILTER

DATE: 10-4-93 CATALOG NO.  
APPROV. T.A.M. 3EHQ8 & 3EHQ8M  
CAD NO. 3EHQ8.01