



Technical Data:

Case Material .....	PA GF black
Switch Lever Material .....	PA GF red
Min.Insulation Resistance .....	100MΩ
Dielectric Withstanding Voltage .....	1050V-1min.
Max.Contact Drop during Resistive Load .....	150mV
Voltage .....	up to 32VDC
Duty Rating .....	2x 300A
Overload .....	2x 500A-180sec.
.....	2x 1000A-30sec.
Sealing .....	IP 67/ IEC 529
Vibration .....	4G/ 50-2000Hz
Shock G-Lever .....	6G/ 11ms
Weight .....	~420g / 0.93 pound
Temperature Range .....	-40°C to +85°C
Wire Section (At Nominal Load) .....	min. 95mm <sup>2</sup>
Mounting Position .....	optional
Switch Lever .....	not removeable
Torque (Main Terminals) .....	15-20Nm

For this drawing we reserve the copyright in accordance with DIN ISO 16016

	Date	Name
Create	17.05.2006	Mielk
Edited	03.03.2020	Seege
Check	10.03.2020	Grind

mm ↔	Scale 1:2
General Tolerances DIN ISO 2768 mK	



Drawing No:

35-323-151-R

NSN: