



CONVERSION CHART	
INCH	MM
.010	0.25
.020	0.51
.031	0.79
.098	2.49
.126	3.20
.134	3.40
.142	3.61
.146	3.71
.197	5.00
.276	7.01
.398	10.11
.402	10.21
.579	14.71
.661	16.79



CIRCUIT DIAGRAM

SPECIFICATIONS:

MATERIALS:
CASE: STEEL.
ACTUATOR: POLYCARBONATE.
MOVABLE CONTACT: SILVER OVER NICKEL OVER COPPER ALLOY.
STATIONARY CONTACT: SILVER OVER NICKEL OVER COPPER ALLOY.
TERMINALS: SILVER OVER NICKEL OVER COPPER ALLOY.

ELECTRICAL:
CONTACT RATING: 250mA 125V AC
150mA 12V DC
INITIAL CONTACT RESISTANCE: 30 MILLIOHMS MAX.
INSULATION RESISTANCE: 500 MEGOHMS MIN.
DIELECTRIC STRENGTH: 500 VOLTS RMS @ SEA LEVEL.
LIFE EXPECTANCY: 10,000 CYCLES

MECHANICAL:
ACTUATION FORCE: 250g +150g -100g.

ENVIRONMENTAL:
OPERATING TEMPERATURE: +14°F TO +140°F
(-10°C TO +60°C)
STORAGE TEMPERATURE: +14°F TO +140°F
(-10°C TO +60°C)

NOTES:

1. INTERPRET DRAWING PER ASME Y14.5M-1994.

OUTLINE DRAWING

SPECIFICATIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE

THIS IS A C.A.D. GENERATED DRAWING. DO NOT MAKE MANUAL REVISIONS TO MASTER.



REV.	2	3	4	5
REVISIONS				
DEDED SPEC'S				
PN073				
S: 10-3-83				
PP'D:				
DD ACTION TO SPECS				
CO#				
S: 10-13-83				
PP'D:				
REVISED & REDRAWN				
CO# 982-94				
E.K 12-23-94				
PP'D: K.L.L. 12-29-94				
REVISED				
CO# 392-95				
W: 5-20-95				
PP'D: J.L.C. 6-1-95				

THIRD ANGLE PROJECTION

TOLERANCES (EXCEPT AS NOTED)
ANGULAR =
DECIMAL .XX =
DECIMAL .XXX = ±.010
DECIMAL .XXXX =

AUGAT CONFIDENTIAL
This document contains information which is the exclusive property of Augat Inc. Distribution, reproduction or use by others is not permitted without the expressed written consent of Augat

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES ON JUST SCALE PRINT		
FILENAME	DIRECTORY	PROJECT
80397.DWG	SLSWCH	
MATERIAL: SEE SPECIFICATIONS		
FINISH: SEE SPECIFICATIONS		

ORIGINAL DATE OF DRAWING:	8-12-77
DRAWN:	B. BUCKHEIT
DATE:	8-12-77
CHECKED:	
DATE:	
APPROVED:	
DATE:	
CODE IDENT. NO.	91506
DWG. SIZE:	B

AUGAT INC. 33 Perry Avenue, Attleboro, Mass. 02703

TITLE: SLIDE SWITCH (SLS-230-PC) DP 3 POS.

DWG. NO: 80397

REV: 5

PRODUCT CODE: C16