



2

S



RECOMMENDED LAYOUT FOR
.062 P.C. BOARD

1. PARTS COMPLY WITH TE SOLDERABILITY SPEC. NO. 109-11-3.
2. CONTACT IS PLATED OVERALL WITH .000050 NICKEL, THEN .000030 GOLD OVER CONTACT LENGTH INDICATED AND TIN PLATED ON SOLDER TAIL END.
3. DIMENSION SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.

SUPERSEDED BY
2-1586544-0

2-380991-0 NYLON - NATURAL COPPER ALLOY - GOLD

1-380991-0 NYLON - NATURAL COPPER ALLOY - PRE-TIN
ASSEMBLY NO. H56. MATL & COLOR. PIN MATL & FINISH.

CUSTOMER COPY
REFERENCE ONLY

REVISION RECORD				
LTR	REVISION	DR	CHK	DATE
T4	REVISED PER ECR-21-117185	PJ	VS	25OCT 2021
T3	REVISED PER ECR-18-008156	JB	DZ	19JUN 2018
T2	REVISED PER ECR-13-008342	AV	RP	12NOV13
T1	REVISED PER ECO-11-005294	RK	HMR	08APR11

NUMBER
166085

REQUIRED PER ASSEMBLY									

DR 6-12-73
9. Edman

CHK 6-13-73
E. Cramer

DE

APP 6/13/73
C. M. P. [Signature]

MATERIAL AND FINISH
SEE-TABLE

WIRE - RANGE - INSULATION
- # -

TOLERANCE EXCEPT AS NOTED
±.015 ±1°0'

SCALE
#

NAME
10 CIRCUIT MATE-N-LOK P.C. BOARD PIN HEADER

TE Connectivity

CLASS #

TYPE #

LOC CM B

NO 380991

RIV T4

PRINTED IN U.S.A.
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.