



Thermofit[®] Molded Parts
 Specification Control Drawing
 Limited Distribution

Part Number : 382C302-X-01
 Description : Slimline Transition, "Y"

NOTES

- All dimensions are in $\frac{\text{inches}}{\text{millimeters}}$
 - Dimensions appearing in table are as follows:
 a - As Supplied
 b - After Unrestricted Recovery
 - Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
- A** Wall thickness will not be measured in transition area.



PART NUMBER	H		J		K		S Norm b	P & R Norm b	HO & JO $\pm 15\%$ b	KKO $\pm 15\%$ b	KO $\pm 15\%$ b	W Norm b
	Min a	Max b	Min a	Max b	Min a	Max b						
382C302-X-01	1.35 [34,4]	.45 [11,4]	.90 [22,9]	.45 [11,4]	.50 [12,7]	.20 [5,1]	2.48 [63,0]	1.73 [43,9]	.87 [22,1]	.65 [16,5]	1.62 [41,1]	.05 [1,3]

**If this document is printed it becomes uncontrolled.
 Check for the latest revision.**

Raychem

RAYCHEM CORPORATION
 300 CONSTITUTION DRIVE
 MENLO PARK, CALIFORNIA 94025

Revision : A
 Date : 6/03/94

Part Number : 382C302-X-01
 Description : Slimline Transition, "Y"

Thermofit[®] Molded Parts
 Specification Control Drawing
 Limited Distribution

Part Number : 382C302-X-01
 Description : Slimline Transition, "Y"

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-50	Flexible VPB	RT-1313			
-51	Flexible EPB	RT-1321			
-71	Flexible Polyolefin	RT-1316			

ORDERING INFORMATION

382C302 -X -01 /XXX

Base part number _____

Material dash number _____
 (See Compatability Chart)

Modification number _____
 (If necessary, see front of scd binder for a complete list)

Adhesive slash number _____
 (If necessary, see Compatability Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Raychem

RAYCHEM CORPORATION
 300 CONSTITUTION DRIVE
 MENLO PARK, CALIFORNIA 94025

Revision : A
 Date : 6/03/94

Part Number : 382C302-X-01
 Description : Slimline Transition, "Y"