


PART NUMBER	PLATING SOCKET BODY	PLATING HOOD
38943-22/38943-20/ 38943-16/38943-12	.000050 MIN. GOLD PER MIL-G-45204 OVER NICKEL	PASSIVATED
38943-22L/38943-20L/ 38943-16L/38943-12L	SELECTIVE PLATING PER SAE-AS39029	PASSIVATED

CI

C 38943-*

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	REVISED PER E.O. C2942	971020	BJH
C	REVISED PER E.O. C8286	110708	J.P.F.



DEUTSCH PART NO. * *	MILITARY PART NO.	COLOR BANDS			SIZE	WIRE GAGE RANGE	RECOMMENDED STRIP LENGTH	CRIMP TOOL		A MIN.	B MIN.	C MAX.
		1ST	2ND	3RD				MS TOOL	POSITIONER			
38943-22 38943-22L	MIL-C-39029/56-348	ORANGE	YELLOW	GRAY	22D	22,24,26,28	.160 TO .190	M22520/2-01 M22520/7-01	M22520/2-07 M22520/7-05	.141	.0335	.048
38943-20 38943-20L	MIL-C-39029/56-351	ORANGE	GREEN	BROWN	20	20,22,24	.230 TO .260	M22520/1-01 M22520/2-01 M22520/7-01	M22520/1-04 M22520/2-10 M22520/7-08	.209	.046	.070
38943-16 38943-16L	MIL-C-39029/56-352	ORANGE	GREEN	RED	16	16,18,20	.230 TO .260	M22520/1-01 M22520/7-01	M22520/1-04 M22520/7-04	.209	.066	.103
38943-12 38943-12L	MIL-C-39029/56-353	ORANGE	GREEN	ORANGE	12	12 AND 14	.230 TO .260	M22520/1-01	M22520/1-04	.209	.098	.151

PROPERTY OF DEUTSCH E.C.D.
THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT SHALL NOT BE DISCLOSED, DUPLICATED,
NOR USED IN WHOLE OR IN PART FOR ANY PUPOSE OTHER THAN TO EVALUATE THIS DRAWING

3. MATERIAL: SOCKET BODY - COPPER ALLOY
SOCKET HOOD - STAINLESS STEEL
2. FINISH: SEE TABLE C2
1. DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES DECIMALS XXX ±.005 ANGLES ±0° 30' 0" T.I.R. .010 PARTS TO HAVE NO BURRS OR SHARP EDGES	SIGNATURE & DATE		CONTACT, SOCKET		CP	---	MATL CODE	61
	DR	D. WHITACRE 820816			CRIMP TYPE SAE-AS39029/56		DEUTSCH ENGINEERED CONNECTING DEVICES 250 EDDIE JONES WAY OCEANSIDE, CA 92058	
	CHK	TIM HOLT 820819						
	MATERIAL	PE	J. GILLS 820818	ENVELOPE		A DWS SIZE	38943-*	
	FINISH	APPD	A.R. 110708					
	SCALE	7.000	WT	NONE			CODE 11139	SHEET OF

38943-XX-ENV