


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELAESE	05DEC2018	BW	SV

D



C

B


A



SECTION B-B



SECTION A-A



- 1 ALL DIMENSIONS PER STANDARD APPLICATION SPEC 114-2046 EXCEPT AS NOTED.
- 2 MATERIAL PER CUSTOMER APPLICATION AND CONSULTATION WITH TE ENGINEERING. TE RECOMMENDS PA66 GF25.
- 3 FINISH (COLOR) PER CUSTOMER AND CONSULTATION WITH TE ENGINEERING.
- 4 IT MUST BE GURANTEED THAT THE MAGNET WIRE CAN TOUCH THE GROUND OF SLOT AND ANVIL. COIL WINDINGS OR OTHER PARTS HAVE TO BE LOWER THAN THE WIRE SLOT OF CAVITY TO GURANTEE OPTIMIZED CONNECTIONS.
- 5 DRAFT ANGLES MUST BE HELD WITHIN THE FEATURE TOLERANCE.

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05DEC2018 CHK BASVESH WARAD VIJAI 05DEC2018 APVD VIJAI 05DEC2018	TE Connectivity		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CAVITY DETAIL, CONNECTING TAB, MAG-MATE	
0 PLC ± 1 PLC ± 2 PLC ±.13 [.005] 3 PLC ± 4 PLC ± ANGLES ±1° FINISH		PRODUCT SPEC - APPLICATION SPEC 114-2046 1 WEIGHT - CUSTOMER DRAWING		SIZE A2 CAGE CODE - DRAWING NO 411-106396 RESTRICTED TO -	
SCALE 9:1		SHEET 1 OF 1		REV A	