SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA 22.2, # 8 VDE APPROVED: EN 133200

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 3 AMP/40°C, 120/250VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND: 0.22mA @ 120V, 60Hz 0.38mA @ 250V, 50Hz

OPERATING AMBIENT TEMP. RANGE: -10° C TO $+40^{\circ}$ C @ RATED CURRENT, Ir.

IN AN AMBIENT, I_0 , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_0 , IS AS FOLLOWS: $I_0 = I_0 - \sqrt{100 - I_0}$ $I_0 = I_r - \sqrt{\frac{100 - T_0}{20}}$

LINE TO LINE:

0.101µF ±20% DISCHARGE RESISTOR: 1.5M \(\triangle) L/G AND L/L I.R

TEST SPECIFICATIONS:

INDUCTANCE: 1.99mH NOMINAL

NO DISCHARGE RESISTOR:

LINE TO GROUND:

6000M₁ (MIN.) @ 100VDC,

CATALOG # 3EGS1-1

ECD # APPRVD. DATE ELC

117JUL07

20°C AND 50% RH

RECOMMENDED RECEIVING INSPECTION HIPOT:

8 SECONDS

CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C) 0.0053µF ±20%

LINE TO GROUND: 1500VAC OR 2250VDC FOR 1 MINUTE


LINE TO LINE: 1450VDC FOR 1 MINUTE

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES Ir FOR

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



	50a-50a(MINIMUM) INSERTION LOSS											
	FREQUENCY MHz	0.01	0.05	0.10	0.15	0.5	1.0	3.0	5.0	10	30	
	COMMON dB	-	10	15	19	30	36	-	48	50	53	
	DIFF. dB	1	-	-	2	11	14	25	38	44	40	

THIRD ANGLE PROJECTION						
UNLESS OTHERWISE SPECIFIED,						
TOLERANCE TO BE ±.025						
MATERIAL &	FINISH:	AS SUPPLIED				

TIMIERIAE WITHISH: NO SBITETED
This document is proprietary to CORCOM INC
and is not to be reproduced nor used for
manufacturing purposes except on CORCOM'S
prior written consent.



CUSTOMER DRAWING 3EGS1-1

TYCD: 0-6	5609117-3		
SCALE: NTS	DATE: 140CT03	CATALOG NO.	REV.
DRW. BY: JF	DRIG: KAW	3EGS1-1	C1