

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .


© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	/	07MAY2019	E.Z	W.H

GOLD PLATING AREA



NOTES:

1. SHIELD FINGER:



MATERIAL: COPPER ALLOY, 0.15±0.01mm THK.

PLATING FINISH: GOLD PLATING 2u" MIN ON THE CONTACT AREA,
MATTE TIN PLATING 100u" MIN ON THE FOOT AREA,
ALLOY NICKEL PLATING 30u"~50u" OVER ALL

2. CURRENT RATING: 1 AMP.


3. THEPERATURE RATING: -40°C TO +105°C.

5.0±0.2



5.3

Matte Tin PLATING AREA



P/N: 440423-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Eliana.Zhang 07MAY2019

CHK Wenke He 07MAY2019

APVD Wenke He 07MAY2019

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

SHIELD FINGER 5025


SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=440423

SCALE 1:1 SHEET 1 OF 2 REV A

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.15
2 PLC ± 0.10
3 PLC ± 0.05
4 PLC ± -
ANGLES ± 2°

MATERIAL

FINISH

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - TE Connectivity Ltd.


ALL RIGHTS RESERVED.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

NOTES:

1. APPLICATION: SHIELD FINGER 5025 ON CONTINUOUS TAPES.
2. NO. OF PKG: 10 REEL MAX.
3. MATERIAL : BOX: CARDBOARD
CARRIER TAPE : ACRYLIC FILM
TOP TAPE : PET FILM
REEL : PLASTIC
4. DIMENSION: BOX: 340mmX340mmX224mm
LABEL: 60mmX80mm
REEL: Ø330mmX21.2mm
5. GENERAL TOLERANCE : $\pm 0.3\text{mm}$
6. PACKING STYLE : 1500pcs/REEL
7. TAPES DIMENSION



8. REEL DIMENSION : REFERENCE ONLY



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Eliana.Zhang 07MAY2019

CHK Wenke He 07MAY2019

APVD Wenke He 07MAY2019

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 0

CUSTOMER DRAWING



TE Connectivity

NAME

SHIELD FINGER 5025

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=440423

SCALE 1:1 SHEET 2 OF 2 REV A

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± 2°

MATERIAL
SEE NOTESFINISH
SEE NOTES