




1. PARTS PACKAGED UNASSEMBLED
- 2 CENTER CONTACT CRIMP: USE DANIELS HMR TOOL AFM8 OR AMP HAND TOOL 601966-1 WITH POSITIONER KI288S.
- 3 BRAID CRIMP: USE DANIELS HAND TOOL HX4 WITH DIESET YI96 CAVITY A OR AMP HAND TOOL 35940-1 WITH DIESET 58483-1 CAVITY B

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J. BAKER 27AUG98	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES		CHK J. WEAVER 27AUG98			
		APVD J. WEAVER 27AUG98	NAME -		
		PRODUCT SPEC -	PIN, COAXIAL, HIGH PERFORMANCE, SIZE 5, ARINC, 75 Ohm		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-443971
MATERIAL -		WEIGHT -	SCALE 10:1		
		CUSTOMER DRAWING	SHEET 1	OF 1	REV A