


4

3

5



γ	



Р	LTR	DESCRIPTION	DATE	DWN	APVD
	J	ECO-14-015233	27APR2015	LL	SH
	JI	REVISED AS PER ECR-23-169440	20APR2023	JK	WH

1

MATERIAL: HOUSING - HIGH TEMPERATURE NYLON, BLACK, UL 94V-O. TERMINALS - 0.25[.010] THICK PHOSPHOR BRONZE PLATED WITH 3.81µm[.000150] MINIMUM THICK BRIGHT TIN-LEAD IN SOLDER AREA, I.27µm[.000050] MINIMUM GOLD IN LOCALIZED PLATE AREA. ENTIRE TERMINAL PLATED WITH 1.27µm[.000050] MINIMUM THICK NICKEL. SHIELD - 0.2[.0079] THICK COPPER ZINC ALLOY, PREPLATED WITH 2.03µm [.000080] MIN THICK BRIGHT TIN OVER I.27µm [.000080] MIN THICK NICKEL

2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68,


 $\boxed{3}$ this dimension represents the total height of the connector FROM THE TOP OF THE PC BOARD.


4. PACKAGED 66 ASSEMBLIES PER PVC TRAY, 396 PER BOX.

5. DIELECTRIC WITHSTANDING VOLTAGE BETWEEN SHIELD AND TERMINAL

ORIENTED AND LOCATED APPROXIMATELY AS SHOWN. LASER PRINTING. TEXT HEIGHT APPROXIMATELY 2MM. FIRST 2 DIGITS = LAST 2 DIGITS OF YEAR NEXT 2 DIGITS = MANUFACTURING WORK WEEK LAST DIGIT = DAY OF WEEK WITH SUNDAY = I

MATERIAL: HOUSING - HIGH TEMPERATURE NYLON, BLACK, UL 94V-O. TERMINALS - 0.25[.010] THICK PHOSPHOR BRONZE PLATED WITH 3.81µm[.000150] MINIMUM THICK MATTE TIN IN SOLDER AREA, I.27µm[.000050] MINIMUM GOLD IN LOCALIZED PLATE AREA. ENTIRE TERMINAL PLATED WITH I.27µm[.000050] MINIMUM THICK NICKEL. OUTER SHIELD AND INNER SHIELD - 0.2[.0079] THICK COPPER ZINC ALLOY, PREPLATED WITH I.27µm [.000050] MINIMUM THICK NICKEL AND HOT TIN DIP ON PCB GROUND TABS.





		/7	406732-2
	obsolete —		406732-1
		MATERIAL/FINISH	PART NUMBER
CONTROLLED DOCUMENT. DWN L. VARSIK	14FEB01 14FEB01	TE TE CON	nnectivity
TOLERANCES UNLESS OTHERWISE SPECIFIED: L. VARSIK 0 PLC ±- APVD 1 PLC ±- PRODUCT SPEC 2 PLC ±0.13[.005] 108-1163 3 PLC ±- APPLICATION SPEC		JLAR JACK ASSEMBLY, DSITION, SHIELDED, I EL TABS, WITHOUT POS	
4 PLC ±- 114-2048 ANGLES ±- 114-2048 FINISH WEIGHT 3.4	grams A 1 0 0	e code drawing no 779 C = 406732	RESTRICTED TO
- CUSTOMER DRAWI	NG	SCALE 8.1 SHEE	T OF REV



А