

SPECIFICATION CONTROL DRAWING

44B4831

TITLE THREE CONDUCTOR CABLE, JACKETED, 600 VOLT	Date 4-2-07	Revision A
This specification sheet forms a part of the latest issue of Raychem Specification 55A.		

COMPONENT WIRES - 44A0811

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE



CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
		MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
44B4831-24-*	24	.006	.008	.133	.139	11.1
44B4831-22-*	22	.006	.008	.150	.157	15.1
44B4831-20-*	20	.006	.008	.167	.176	20.4
44B4831-18-*	18	.006	.008	.189	.198	28.6
44B4831-16-*	16	.006	.008	.208	.219	35.4
44B4831-14-*	14	.007	.009	.251	.264	53.6
44B4831-12-*	12	.007	.009	.290	.305	77.5
44B4831-10-*	10	.008	.010	.355	.373	119.
44B4831- 8-*	8	.009	.011	.484	.508	207.
44B4831- 6-*	6	.010	.012	.594	.624	324.
44B4831- 4-*	4	.014	.016	.723	.756	500.
44B4831- 2-*	2	.017	.020	.904	.949	805.
44B4831- 0-*	0	.021	.024	1.11	1.16	1228.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C
 Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms) at sea level
 ACCELERATED AGING: 300 ± 3°C for 7 hours
 BLOCKING: 150 ± 3°C for 6 hours
 DIELECTRIC WITHSTAND: 2500 volts (rms), 60 Hz, 1 minute
 FLAMMABILITY (Procedure 1): 3 seconds (maximum);
 3 in. (maximum); no flaming of facial tissue
 JACKET COLOR: White preferred
 JACKET ELONGATION AND TENSILE STRENGTH:
 Elongation, 50% (minimum)
 Tensile Strength, 5000 lbf/in² (minimum)

LIFE CYCLE: 200 ± 3°C for 168 hours
 LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

PART NUMBER:
 The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

1/ Example: AWG 20, black, brown and red component wires;
 white jacket: 44B4831-20-0/1/2-9

NOTE: Nominal values are for information only.
 Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
 Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL	Tyco Electronics	Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297
THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.			