








P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	23AUG2023	NK	JDB
	A2	DRAWING RE-CREATED IN CREO	20OCT2023	NK	JDB



1. COPLANARITY OF ALL CLIPS <=0.1mm
 2 PART; 100 PCS. IN BUBBLE BAGS/BULK



INSPECTION LEVEL 1: CONTROL CHART REQUIRED

(1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED


INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED

(7) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

(/3) PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

			
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
4	-	PINS	2
1	-	M8 HOUSING	1
474231-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 21AUG2023 CHK M SZELAG 23AUG2023 APVD J DE BRUIJN 23AUG2023		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015		NAME M8 FEMALE, A CODE, 4P, 16.25MM THR V	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781	
MATERIAL - -		FINISH -		WEIGHT -	
CUSTOMER DRAWING				SIZE A 3	CAGE CODE 00779
SCALE 5:1				DRAWING NO C=474231-E	RESTRICTED TO -
SHEET 1 OF 1				REV A2	