

SPECIFICATION CONTROL DRAWING

44A121X

TITLE ONE CONDUCTOR CABLE, RADIATION-CROSSLINKED, POLYALKENE-INSULATED, SHIELDED, JACKETED, LIGHTWEIGHT, GENERAL PURPOSE

Date 03-11-04

Revision D

This specification sheet forms a part of the latest issue of Raychem Specification 44.




TABLE I. CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lb/1000ft)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
44A121X-26*	26	40	.005	.007	.068	.073	4.6
44A121X-24*	24	38	.005	.007	.078	.084	6.5
44A121X-22*	22	38	.006	.008	.088	.094	8.3
44A121X-20*	20	36	.006	.008	.100	.105	11.7
44A121X-18*	18	36	.006	.008	.111	.118	15.2
44A121X-16*	16	36	.006	.008	.119	.126	17.9
44A121X-14*	14	36	.006	.008	.136	.143	24.3
44A121X-12*	12	36	.006	.008	.155	.163	33.3
44A121X-10*	10	36	.007	.009	.186	.194	49.7
44A121X- 8*	8	36	.007	.009	.246	.255	81.3
44A121X- 6*	6	36	.008	.010	.296	.307	119.
44A121X- 4*	4	36	.008	.010	.350	.369	180.

TABLE II. CABLE PERFORMANCE DETAILS

PART NUMBER 1/	BEND TESTING			
	MANDREL DIAMETER (inch) (± 3%)		WEIGHT (lb) (± 3%)	
	LIFE CYCLE, IMMERSION AND ACCELERATED AGING	COLD BEND	LIFE CYCLE, IMMERSION AND ACCELERATED AGING	COLD BEND
44A121X-26*	3.00	3.00	.185	1.50
44A121X-24*	3.00	3.00	.185	3.00
44A121X-22*	3.00	3.00	.185	3.00
44A121X-20*	3.00	3.00	.250	4.50
44A121X-18*	3.00	3.00	.250	4.50
44A121X-16*	3.00	3.00	.500	6.00
44A121X-14*	6.00	6.00	.500	6.00
44A121X-12*	6.00	6.00	.750	6.00
44A121X-10*	6.00	6.00	1.00	6.00
44A121X- 8*	6.00	6.00	1.50	7.50
44A121X- 6*	10.0	10.0	1.50	12.0
44A121X- 4*	10.0	10.0	1.50	12.0

NOTE: Nominal values are for information only.
Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx"). OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oaks Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 1000 volts (rms) at sea level

ACCELERATED AGING: 300 ± 3°C for 6 hours

BLOCKING: 150 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 3000 volts (rms), 60 Hz, 1 minute

FLAMMABILITY: 30 seconds (maximum); 3 in. (maximum); no flaming of facial tissue

IMMERSION: Diameter increase 5% (maximum); no cracking, no dielectric breakdown

JACKET COLOR: White preferred

JACKET CONCENTRICITY: 70% (minimum)

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 200% (minimum)

Tensile Strength, 4000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1.5 kV (rms)

Impulse Dielectric Test, 6.0 kV (peak)

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (Post Environmental):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "X" in the part numbers on page 1 shall be replaced by the applicable conductor material designator as follows:

- 1 tin-coated copper
- 2 silver-coated copper
- 3 nickel-coated copper
- 4 silver-coated high strength copper alloy
- 6 nickel-coated high strength copper alloy

The "*" in the part numbers on page 1 shall be replaced by color code designators with a dash separating the component wire color from the jacket color.

1/ Example: AWG 20, tin-coated copper, white component wire;
white jacket: 44A1211-20-9-9

1/ see footer section on page 1