


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	25AUG2023	NK	JDB
	C1	DRAWING RE-CREATED IN CREO	28DEC2023	NK	JDB
	C2	REEL CORE DIA CHANGE	24 JUL2024	KA	LET



INSPECTION LEVEL 1: CONTROL CHART REQUIRED





1 PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED

2 PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

3 PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST


INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3




TRAY PACKAGING: PACKAGING UNIT 50 PCS

(325)

CONSIDER MOUNTING POSITION: CENTER BACK





TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS



CONSIDER MOUNTING POSITION; PEG RIGHT

REEL OFF DIRECTION



SCALE 2:1
3D VIEW

1. DRAWING SPECIFICATION ACCORDING TO DOCUMENT 5_3_16-DOC-1806-00915

2. COPLANARITY OF ALL CLIPS ≤ 0.1MM

OBSOLETE

-	1	-	TOP COVER	7
-	1	-	TRAY PACKAGING	6
1	1	-	TAPE AND REEL	5
1	1	-	SOLDER CLIP LEFT	4
1	1	-	SOLDER CLIP RIGHT	3
8	8	-	PINS	2
1	1	-	HOUSING	1

474681-E	474680-E	REV	DESCRIPTION	ITEM NO.
-	-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)	-

QTY

PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 26JUL2023	 TE Connectivity	
DIMENSIONS: mm		CHK M SZELAG 28JUL2023		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015	APVD J DE BRUIJN 28JUL2023	NAME M12 FEMALE, A CODE, 8P, 17MM THR	
		PRODUCT SPEC 108-94887	-	
MATERIAL - -	FINISH -	APPLICATION SPEC 114-94781	SIZE A2	CAGE CODE 00779
		WEIGHT -	DRAWING NO C=474680-E	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1
			REV C2	