


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	25AUG2023	NK	JDB
	D1	DRAWING RE-CREATED IN CREO	28DEC2023	NK	JDB
	D2	REEL CORE DIA CHANGE	24 JUL2024	KA	LET

D




INSPECTION LEVEL 1: CONTROL CHART REQUIRED
① PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
② PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY





③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3

TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS




C




CONSIDER MOUNTING POSITION; PEG RIGHT


B




PCB-LAYOUT PROPOSAL



SCALE 2:1
3D VIEW



- DRAWING SPECIFICATION ACCORDING TO DOCUMENT 5_3_16-DOC-1806-00915
- COPLANARITY OF ALL CLIPS $\leq 0.1\text{MM}$



1	-	TAPE AND REEL	6
1	-	PAD	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
12	-	PINS	2
1	-	HOUSING	1
484074-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY		PARTS LIST	

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 04AUG2023	TE Connectivity			
DIMENSIONS: mm		CHK M SZELAG 07AUG2023				
TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015		APVD J DE BRUIJN 07AUG2023	NAME M12 FEMALE, A CODE, 12P, 17MM SMT V			
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781 WEIGHT -	SIZE A2			
MATERIAL -		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV D2	RESTRICTED TO -

A

A