



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	25AUG2023	NK	JDB
	G1	DRAWING RE-CREATED IN CREO	28DEC2023	NK	JDB
	G2	NOTES AND TOLERANCES UPDATE	05APR2024	NK	JDB
	G3	REEL CORE DIA CHANGE	23JUL2024	KA	LET

TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 75 PCS




CONSIDER MOUNTING POSITION: PEG RIGHT




OBsolete						
1	1	1	-	TAPE & REEL		6
1	-	1	-	PAD		5
1	1	1	-	SOLDER CLIP LEFT		4
1	1	1	-	SOLDER CLIP RIGHT		3
4	4	4	-	PINS		2
1	1	1	-	HOUSING		1
284784-E	284809-E	484790-E	REV	DESCRIPTION		ITEM NO.
-	-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)			
QTY			PARTS LIST			

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)
 *=VERSION: WITH CUT-IN, WITHOUT SEAL.



SCALE 2:1
3D VIEW




INSPECTION LEVEL 1: CONTROL CHART REQUIRED
 (1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF
 PROCESS CAPABILITY IS NOT ACHIEVED


INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
 (72) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3



PCB-LAYOUT PROPOSAL



1. DRAWING SPECIFICATION ACCORDING TO
DOCUMENT 5_3_16-DOC-1806-00915

2. COPLANARITY OF ALL CLIPS $\leq 0.1\text{MM}$

 PART; 100 PCS. IN BUBBLE BAGS/BULK

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11AUG2023 N K NIKHIL CHK 13AUG2023 M SZELAG APVD 13AUG2023 J DE BRUIJN		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED: DIM. FOR INFORMATION ISO 8015		NAME	
mm		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		M12 MALE, A CODE, 4P, 10.5MM SMT V * - -	
		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781 WEIGHT -		SIZE	CAGE CODE
MATERIAL		CUSTOMER DRAWING		DRAWING NO	
-				A2 00779 C=484790-E	
-				SCALE	SHEET
				5:1	1 of 1
				REV	G3